

# Swepe r-Frame

Symmetrical and fully flat frame made from up to >30% recycled plastic



## Product Description

The Swepe r-Frame has a sleek, symmetrical, fully flat design. The frame can effortlessly be flipped for cleaning with the second side of the mop. Touchless mop removal is possible with two easy-to-use peelers – simplicity for either left or right-handers.

The Swepe r-Frame was designed with ergonomics and sustainability in mind: it is designed as part of an ErgoCert certified ergonomic system and carries the prestigious Plastica Seconda Vita certification for use of second life plastic.

## Application

With the new Swepe r-Frame, cleaners do not have to touch contaminated and dirty mops whilst taking them off the frame. The frame can be used with all Swepe r-Pro mops as well as with Swepe Duo mops in 35 and 50 cm. As part of the next generation Swepe system, it can be used wherever maximum hygiene and cleanliness are paramount. On floors, walls, staircases and even ceilings.

## Advantages

- ✓ Maximized flatness for greater floor contact
- ✓ Symmetrical design: Two peelers for faster, hands-free mop exchange
- ✓ Hygienic construction: no raised axis, less dirt traps

- ✓ Made from up to >30% recycled plastic
- ✓ Awarded the Plastica Seconda Vita certification
- ✓ Recognized by ErgoCert as part of an ergonomic system when used with Swepe Pro mops and either the Telescopic Handle or r-Ergonomic Handle

## How to use

- ✓ Take the mop out of the pre-box (by using the finger loop) and hold frame by the hand grip to stabilize the frame whilst putting mop around one end of frame and pulling by the mop finger loop to put mop securely on the other end of the frame
- ✓ Adjust telescopic handle to correct height
- ✓ Start mopping in guided cleaning direction on the mop indicated by the arrow – for r-Duo mops, on the arrow is on the finger loop and on r-Single mops the arrow is on the mop backing

## For mop change:

- ✓ Position the frame over the trolley laundry bag whilst holding the handle approx. 20 cm underneath the frame
- ✓ Pull one peeler on one end of the frame using the finger-pull to release the mop
- ✓ Drop mop head into laundry bag
- ✓ Close the peeler before putting the next mop onto the frame

Description	Size cm	Art.no Case	Packs / case	Art.no Pack	Pieces / Pack
Swepe r-Frame	35	171332	10	171336	1
Swepe r-Frame	50	171333	10	171337	1
Swepe r-Frame	65	171334	10	171338	1
Swepe r-Frame	85	171335	10	171339	1